

Eaton 10250T4067LL-112233X

Catalog Number: 10250T4067LL-112233X

Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Four-position, Maintained, Lever, Blue actuator, 6NO-CNC

General specifications

| | |
|-------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton 10250T pushbutton | 10250T4067LL-112233X |
| UPC | Product Length/Depth |
| 786685106069 | 2 in |
| Product Height | Product Width |
| 2.2 in | 1.9 in |
| Product Weight | Warranty |
| 0.25 lb | 1 year |
| Compliances | Certifications |
| CE Marked | UL Listed |
| | CSA Certified |



Product specifications

Product Category

Selector switch

Contact configuration

6 NO-CNC

Throw type

40 °, left/right

Number of positions

4

Actuator color

Blue

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Size

30.5 mm

Enclosure

NEMA 12

NEMA 3R

NEMA 3

NEMA 4

NEMA 4X

NEMA 13

Bezel

Zinc die cast, chrome

Series

10250T

Type

30.5 mm, Heavy-Duty

Operating mode

Maintained

NEMA rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Non-illuminated

Cam code

Cam 7

Actuator

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T4067LL-112233X



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)