

Eaton 10250T411C21-1-POP

Catalog Number: 10250T411C21-1-POP

10250T, 30.5 mm, Heavy-Duty, Standard, square, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Extended, Red actuator, Black field, POWER ON, Incandescent, transformer light unit, 1NO-1NC, 120 Vac LUV, Chrome bezel, Plastic actuator

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T411C21-1-POP
UPC	Product Length/Depth
782114408568	2.87 in
Product Height	Product Width
1.38 in	1.38 in
Product Weight	Warranty
0.43 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified UL Listed

Catalog Notes

Includes 2 extra lenses: Green and Amber



Product specifications

Contact configuration

1 NO-1 NC

Actuator color

Red

Legend

POWER ON

Actuator material

Plastic

Light unit voltage

120 Vac

Rating

NEMA 3

NEMA 13

NEMA 3R

NEMA 4X

NEMA 4

NEMA 12

Field color

Black

Size

Standard, square

Bezel

Chrome

Series

10250T

Light unit type

Incandescent, transformer

Type

30.5 mm, Heavy-Duty

Operating mode

Momentary

Illumination

Illuminated

Actuator

Extended

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T411C21-1-POP

Quick Selector - 10250T Pilot Devices



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)