

Eaton 10250T411C24

Catalog Number: 10250T411C24

Eaton 10250T pushbutton, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Blue actuator, Incandescent, transformer light unit, Flush, 120 V light unit, Chrome bezel, #755, Plastic actuator

General specifications

| | |
|-------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton 10250T pushbutton | 10250T411C24 |
| UPC | Product Length/Depth |
| 782113757117 | 2.87 in |
| Product Height | Product Width |
| 1.38 in | 1.38 in |
| Product Weight | Warranty |
| 0.01 lb | 1 year |
| Compliances | Certifications |
| CE Marked | CSA Certified |
| | UL Listed |



Product specifications

Special features

10250T series

Actuator color

Blue

Actuator material

Plastic

Light unit voltage

120 Vac

Rating

NEMA 4X

NEMA 13

NEMA 3

NEMA 4

NEMA 3R

NEMA 12

Mounting method

Flush

Bezel

Chrome

LED lamp number

#755

Series

10250T

Light unit type

Incandescent, transformer

Type

30.5 mm Heavy-Duty Watertight/Oiltight

Operating mode

Momentary

Illumination

Illuminated

Application

Pushbutton

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T411C24



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)