

Eaton 10250T411HL

Catalog Number: 10250T411HL

Eaton 10250T pushbutton, 30.5 mm, Class I Division 2, NEMA 3, 3R, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D, Illuminated, Momentary, LED, transformer light unit, Flush, 120 V light unit, Chrome bezel, Bayonet base

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T411HL
UPC	Product Length/Depth
782114552551	2.87 in
Product Height	Product Width
1.38 in	1.38 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified UL 505

Catalog Notes

Unit does not include lamp. Order LED separately to match lens.



Product specifications

LED lamp number

Bayonet base

Special features

10250T series

Series

10250T

Light unit type

LED, transformer

Type

30.5 mm Heavy-Duty Watertight/Oiltight

Operating mode

Momentary

Light unit voltage

120 Vac

Rating

NEMA 12

NEMA 3

NEMA 4

NEMA 4X

NEC Class I Division 2, Groups B, C and D

NEMA 3R

NEMA 13

Illumination

Illuminated

Mounting method

Flush

Application

Pushbutton

Bezel

Chrome

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T411HL



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)