

Eaton 10250T411LAD06

Catalog Number: 10250T411LAD06

Eaton 10250T, 30.5 mm, Heavy-Duty, 40 mm, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Amber actuator, LED, transformer light unit, Flush, 120 Vac light unit, Chrome bezel, Bayonet base, 6 Vac/dc lamp, Plastic actuator

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T411LAD06
UPC	Product Length/Depth
782114709719	2.87 in
Product Height	Product Width
1.38 in	1.38 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed

Product specifications

Special features

10250T series

Actuator color

Amber

Actuator material

Plastic

Light unit voltage

120 Vac

Lamp voltage - min

6 V

Rating

NEMA 12

NEMA 3

NEMA 13

NEMA 4X

NEMA 4

NEMA 3R

Size

40 mm

Mounting method

Flush

Bezel

Chrome

LED lamp number

Bayonet base

Series

10250T

Lamp voltage - max

6 V

Light unit type

LED, transformer

Type

30.5 mm, Heavy-Duty

Operating mode

Momentary

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T411LAD06

Illumination

Illuminated

Application

Pushbutton



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)