

Eaton 10250T414L

Catalog Number: 10250T414L

Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, LED, transformer light unit, Flush, 480 Vac light unit, Chrome bezel, Bayonet base

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T414L
UPC	Product Length/Depth
782114554289	1 in
Product Height	Product Width
1 in	1 in
Product Weight	Warranty
0.1 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed

Catalog Notes

Unit does not include lamp. Order LED separately to match lens.



Product specifications

LED lamp number

Bayonet base

Series

10250T

Light unit type

LED, transformer

Type

Pushbutton

Operating mode

Momentary

Bus material

Zinc die cast

Light unit voltage

480 Vac

Rating

NEMA 4

NEMA 12

NEMA 3

NEMA 4X

NEMA 13

NEMA 3R

Illumination

Illuminated

Mounting method

Flush

Bezel

Chrome

Degree of protection

NEMA 13

NEMA 3R

NEMA 12

NEMA 3

NEMA 4

NEMA 4X

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T414L



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)