

# Eaton 10250T415

Catalog Number: 10250T415

Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Incandescent, transformer light unit, Flush, 600 Vac light unit, Chrome bezel, #755

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T415
UPC	Product Length/Depth
782113225883	2 in
Product Height	Product Width
3.5 in	2.5 in
Product Weight	Warranty
0.1 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed



## Product specifications

### LED lamp number

#755

### Series

10250T

### Light unit type

Incandescent, transformer

### Type

Pushbutton

### Operating mode

Momentary

### Bus material

Zinc die cast

### Light unit voltage

600 Vac

### Rating

NEMA 12

NEMA 13

NEMA 3R

NEMA 4

NEMA 4X

NEMA 3

### Illumination

Illuminated

### Mounting method

Flush

### Bezel

Chrome

### Degree of protection

NEMA 3R

NEMA 4X

NEMA 13

NEMA 4

NEMA 3

NEMA 12

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T415



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)