

Eaton 10250T416

Catalog Number: 10250T416

Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Incandescent, transformer light unit, Flush, 24 Vac light unit, Chrome bezel, #755

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T416
UPC	Product Length/Depth
782113203706	2.4 in
Product Height	Product Width
3.2 in	2.1 in
Product Weight	Warranty
0.35 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified

Product specifications

LED lamp number

#755

Series

10250T

Light unit type

Incandescent, transformer

Type

Pushbutton

Operating mode

Momentary

Bus material

Zinc die cast

Light unit voltage

24 Vac

Rating

NEMA 4X

NEMA 13

NEMA 12

NEMA 4

NEMA 3R

NEMA 3

Illumination

Illuminated

Mounting method

Flush

Bezel

Chrome

Degree of protection

NEMA 4

NEMA 3

NEMA 3R

NEMA 13

NEMA 12

NEMA 4X

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T416



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)