

# Eaton 10250T416H

Catalog Number: 10250T416H

Eaton 10250T, 30.5 mm, Class I Division 2, NEMA 3, 3R, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D, Illuminated, Momentary, Incandescent, transformer light unit, Flush, 24 Vac light unit, Chrome bezel, #755

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T416H
UPC	Product Length/Depth
782114510742	2.5 in
Product Height	Product Width
1.75 in	2.38 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified UL 505

## Product specifications

### LED lamp number

#755

### Series

10250T

### Light unit type

Incandescent, transformer

### Type

30.5 mm, Class I Division 2

### Operating mode

Momentary

### Light unit voltage

24 Vac

### Rating

NEMA 13

NEMA 3

NEC Class I Division 2, Groups B, C and D

NEMA 4

NEMA 4X

NEMA 3R

NEMA 12

### Illumination

Illuminated

### Mounting method

Flush

### Bezel

Chrome

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T416H



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)