

Eaton 10250T419HL

Catalog Number: 10250T419HL

10250T, 30.5 mm, Class I Division 2, NEMA 3, 3R, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D, Illuminated, Momentary, LED, transformer light unit, Flush, 277 Vac light unit, Chrome bezel, Bayonet base

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T419HL
UPC	Product Length/Depth
782114552575	1 in
Product Height	Product Width
1 in	1 in
Product Weight	Warranty
0.1 lb	1 year
Compliances	Certifications
CE Marked	UL 505 CSA Certified

Catalog Notes

Unit does not include lamp. Order LED separately to match lens.



Product specifications

LED lamp number

Bayonet base

Series

10250T

Light unit type

LED, transformer

Type

30.5 mm, Class I Division 2

Operating mode

Momentary

Light unit voltage

277 Vac

Rating

NEMA 4

NEMA 4X

NEC Class I Division 2, Groups B, C and D

NEMA 3

NEMA 13

NEMA 12

NEMA 3R

Illumination

Illuminated

Mounting method

Flush

Bezel

Chrome

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T419HL