

Eaton 10250T4337

Catalog Number: 10250T4337

Eaton 10250T pushbutton, Heavy-Duty, NEMA 4, 4X, 12, 13, Momentary, One indicating light, two pushbuttons, flush, Red actuator, Die cast enc., MOTOR RUN START/STOP, Transformer light unit, Surface, 1NO-2NC, Three elements

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T4337
UPC	Product Length/Depth
782113294926	0.25 in
Product Height	Product Width
7.75 in	3.88 in
Product Weight	Warranty
0.4 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified

Catalog Notes

Enclosure has corrosion resistant coating



Product specifications

Contact configuration

1 NO-2 NC

Actuator color

Red

Legend

MOTOR RUN START/STOP

Number of elements

3

Light unit voltage

110 Vac

Rating

NEMA 12

NEMA 4

NEMA 13

NEMA 4X

Mounting method

Surface

Enclosure material

Die cast

Light unit type

Transformer

Series

10250T

Type

30.5 mm, Heavy-Duty

Operating mode

Momentary

Actuator

One indicating light, two pushbuttons, flush

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T4337



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)