

Eaton 10250T463LGD06-3X

Catalog Number: 10250T463LGD06-3X

Eaton 30.5 mm Heavy-Duty Push-Pull, Assembled, Standard 40 mm Actuator (Lens), Green, Plastic Bus, 2NC, Bayonet base, Illuminated, 6 Vac/Vdc Lamp, LED, transformer, 120 Vac Light Unit, Three-position, Mom. Push/pull, Main. intermediate, 10250T Series

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T463LGD06-3X
UPC	Product Length/Depth
782114715550	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	Catalog Notes
CSA Certified UL Listed	Assembled at Factory



Product specifications

Contact configuration

2 NC

Special features

Factory Assembled

Number of positions

3

Actuator color

Green

Bus material

Plastic

Light unit voltage

120 Vac

Lamp voltage - min

6 V

Rating

NEMA 12

NEMA 3

NEMA 4

NEMA 13

NEMA 4X

NEC Class I Division 2, Groups B, C and D

NEMA 3R

Size

40 mm

Series

10250T

Lamp voltage - max

6 V

Light unit type

LED, transformer

Type

Class I Division 2

Operating mode

Intermediate: maintained

Push: momentary

Pull: momentary

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T463LGD06-3X

Illumination

Illuminated

Actuator

Standard



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)