

# Eaton 10250T463LLS06-3X

Catalog Number: 10250T463LLS06-3X

Eaton 30.5 mm Heavy-Duty Push-Pull, Assembled, Side-lighted 40 mm Actuator, Blue, 2NC, Bayonet base, Illuminated, 6 Vac/Vdc Lamp, LED, transformer, 120 Vac Light Unit, Three-position, Mom. Push/pull, Main. intermediate, 10250T Series

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T463LLS06-3X
UPC	Product Length/Depth
782114715635	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	Catalog Notes
UL Listed CSA Certified	Assembled at Factory



## Product specifications

### Contact configuration

2 NC

### Special features

Factory Assembled

### Number of positions

3

### Actuator color

Blue

### Bus material

Anodized aluminum

### Light unit voltage

120 Vac

### Lamp voltage - min

6 V

### Rating

NEMA 3R

NEC Class I Division 2, Groups B, C and D

NEMA 12

NEMA 4X

NEMA 3

NEMA 13

NEMA 4

### Size

40 mm

### Series

10250T

### Lamp voltage - max

6 V

### Light unit type

LED, transformer

### Type

Class I Division 2

### Operating mode

Push: momentary

Pull: momentary

Intermediate: maintained

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T463LLS06-3X

Illumination

Illuminated

Actuator

Side-lighted



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)