

Eaton 10250T471

Catalog Number: 10250T471

Eaton 10250T pushbutton, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Three-position, Momentary push and pull, maintained intermediate, Incandescent, resistor light unit, 120 V light unit

General specifications

| | |
|-------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton 10250T pushbutton | 10250T471 |
| UPC | Product Length/Depth |
| 782113226026 | 2.4 in |
| Product Height | Product Width |
| 3.3 in | 2.1 in |
| Product Weight | Warranty |
| 0.2 lb | 1 year |
| Compliances | Certifications |
| CE Marked | UL Listed |
| | CSA Certified |

Catalog Notes

Contact blocks 10250T55 and 10250T57 cannot be used with this operator



Product specifications

Special features

10250T series

Series

10250T

Light unit type

Incandescent, resistor

Number of positions

3

Type

30.5 mm Heavy-Duty Watertight/Oiltight

Operating mode

Pull: momentary

Intermediate: maintained

Push: momentary

Light unit voltage

120 Vac

Rating

NEMA 3

NEMA 13

NEMA 4X

NEMA 3R

NEMA 12

NEMA 4

Illumination

Illuminated

Size

30.5 mm

Application

Pushbutton

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T471



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)