

# Eaton 10250T471C22-2S19

Catalog Number: 10250T471C22-2S19

Eaton 10250T pushbutton, 30.5 mm, Heavy-Duty, Standard, square, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Mom., Extended, plastic green actuator, Black field, JOG, Incandescent, resistor light unit, 2NO, 120 Vac/dc light unit, Chrome bezel

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T471C22-2S19
UPC	Product Length/Depth
782113925721	2.87 in
Product Height	Product Width
1.38 in	1.38 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified UL Listed

## Product specifications

### Contact configuration

2 NO

### Special features

10250T series

### Actuator color

Green

### Legend

JOG

### Actuator material

Plastic

### Light unit voltage

120 Vac/dc

### Rating

NEMA 13

NEMA 3R

NEMA 4

NEMA 12

NEMA 4X

NEMA 3

### Field color

Black

### Size

Standard, square

### Bezel

Chrome

### Series

10250T

### Light unit type

Incandescent, resistor

### Type

30.5 mm Heavy-Duty Watertight/Oiltight

### Operating mode

Momentary

### Illumination

Illuminated

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T471C22-2S19

Application

Pushbutton

Actuator

Extended



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)