

Eaton 10250T471H

Catalog Number: 10250T471H

Eaton 10250T pushbutton, 30.5 mm, Class I Division 2, NEMA 3, 3R, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D, Illuminated, Momentary, Incandescent, resistor light unit, Flush, 120 Vac/dc light unit, Chrome bezel, 120MB

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T471H
UPC	Product Length/Depth
782114510858	2.87 in
Product Height	Product Width
1.38 in	1.38 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified UL 505

Product specifications

LED lamp number

120MB

Special features

10250T series

Series

10250T

Light unit type

Incandescent, resistor

Type

30.5 mm Heavy-Duty Watertight/Oiltight

Operating mode

Momentary

Light unit voltage

120 Vac/dc

Rating

NEMA 13

NEMA 12

NEMA 4X

NEMA 4

NEMA 3R

NEC Class I Division 2, Groups B, C and D

NEMA 3

Illumination

Illuminated

Mounting method

Flush

Application

Pushbutton

Bezel

Chrome

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T471H



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)