

# Eaton 10250T472H

Catalog Number: 10250T472H

Eaton 10250T pushbutton, 30.5 mm, Class I Division 2, NEMA 3, 3R, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D, Illuminated, Momentary, Incandescent, resistor light unit, Flush, 240 Vac/dc light unit, Chrome bezel, 120MB

## General specifications

|                         |                         |
|-------------------------|-------------------------|
| Product Name            | Catalog Number          |
| Eaton 10250T pushbutton | 10250T472H              |
| UPC                     | Product Length/Depth    |
| 782114510865            | 2.87 in                 |
| Product Height          | Product Width           |
| 1.38 in                 | 1.38 in                 |
| Product Weight          | Warranty                |
| 0.01 lb                 | 1 year                  |
| Compliances             | Certifications          |
| CE Marked               | UL 505<br>CSA Certified |

## Product specifications

### LED lamp number

120MB

### Special features

10250T series

### Series

10250T

### Light unit type

Incandescent, resistor

### Type

30.5 mm Heavy-Duty Watertight/Oiltight

### Operating mode

Momentary

### Light unit voltage

240 Vac/dc

### Rating

NEMA 4X

NEMA 13

NEMA 3R

NEMA 4

NEMA 12

NEMA 3

NEC Class I Division 2, Groups B, C and D

### Illumination

Illuminated

### Mounting method

Flush

### Application

Pushbutton

### Bezel

Chrome

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T472H



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)