

Eaton 10250T473

Catalog Number: 10250T473

Eaton 10250T pushbutton, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Three-position, Momentary push and pull, maintained intermediate, Incandescent, full voltage light unit, 6 Vac/dc light unit

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T473
UPC	Product Length/Depth
782113226040	2.87 in
Product Height	Product Width
1.38 in	1.38 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified UL Listed

Catalog Notes

Contact blocks 10250T55 and 10250T57 cannot be used with this operator



Product specifications

Special features

10250T series

Series

10250T

Light unit type

Incandescent, full voltage

Number of positions

3

Type

30.5 mm Heavy-Duty Watertight/Oiltight

Operating mode

Push: momentary

Intermediate: maintained

Pull: momentary

Light unit voltage

6 Vac/dc

Rating

NEMA 4

NEMA 4X

NEMA 13

NEMA 3

NEMA 12

NEMA 3R

Illumination

Illuminated

Application

Pushbutton

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T473



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)