

Eaton 10250T476C24

Catalog Number: 10250T476C24

Eaton 10250T pushbutton, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Blue actuator, Incandescent, full voltage light unit, Flush, 24 Vac/dc light unit, Chrome bezel, #757, Plastic actuator

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T476C24
UPC	Product Length/Depth
782113769936	2.87 in
Product Height	Product Width
1.38 in	1.38 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified



Product specifications

Special features

10250T series

Actuator color

Blue

Actuator material

Plastic

Light unit voltage

24 Vac/dc

Rating

NEMA 4

NEMA 4X

NEMA 3

NEMA 12

NEMA 13

NEMA 3R

Mounting method

Flush

Bezel

Chrome

LED lamp number

#757

Series

10250T

Light unit type

Incandescent, full voltage

Type

30.5 mm Heavy-Duty Watertight/Oiltight

Operating mode

Momentary

Illumination

Illuminated

Application

Pushbutton

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T476C24



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)