

# Eaton 10250T480

Catalog Number: 10250T480

10250T, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Three-position, Momentary push and pull, maintained intermediate, Incandescent, resistor light unit, 120 Vac light unit

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T480
UPC	Product Length/Depth
782113347332	1 in
Product Height	Product Width
1 in	1 in
Product Weight	Warranty
0.1 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed

## Catalog Notes

Contact blocks 10250T55 and 10250T57 cannot be used with this operator



## Product specifications

### Series

10250T

### Light unit type

Incandescent, resistor

### Number of positions

3

### Type

30.5 mm, Heavy-Duty

### Operating mode

Pull: momentary

Push: momentary

Intermediate: maintained

### Light unit voltage

120 Vac

### Rating

NEMA 3R

NEMA 4X

NEMA 3

NEMA 13

NEMA 4

NEMA 12

### Illumination

Illuminated

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T480



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia