

# Eaton 10250T567

Catalog Number: 10250T567

Eaton 30.5 mm Heavy-Duty Push-Pull Unit, Class I Division 2, Standard Actuator, Plastic Bus, Illuminated, Lamp #755, Incandescent, transformer, 480 Vac Light Unit, Two-position, Maintained push and pull, 40 mm button, 10250T Series

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T567
UPC	Product Length/Depth
782114960288	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	
UL Listed	
CSA Certified	



## Product specifications

### Series

10250T

### Light unit type

Incandescent, transformer

### Number of positions

2

### Type

Class I Division 2

### Operating mode

Pull: maintained

Push: maintained

### Light unit voltage

480 Vac

### Rating

NEMA 3

NEMA 13

NEMA 12

NEMA 4X

NEMA 4

NEMA 3R

NEC Class I Division 2, Groups B, C and D

### Illumination

Illuminated

### Actuator

Standard

## Resources

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Eaton Specification Sheet - 10250T567](#)