

Eaton 10250T579C63-13X

Catalog Number: 10250T579C63-13X

Eaton 10250T, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, 2-position, Maintained push and pull, Side-lighted, Red actuator, EMERGENCY STOP, Incandescent, full voltage light unit, 1NO-3NC, 24 Vac/dc light unit, Chrome bezel

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T579C63-13X
UPC	Product Length/Depth
782114960301	2.63 in
Product Height	Product Width
1.78 in	1.78 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	UL Listed CSA Certified

Catalog Notes

Parts assembled from factory.



Product specifications

Contact configuration

1 NO-3 NC

Number of positions

2

Actuator color

Red

Legend

EMERGENCY STOP

Light unit voltage

24 Vac/dc

Rating

NEMA 12

NEMA 4X

NEMA 3

NEMA 13

NEMA 3R

NEMA 4

Bezel

Chrome

Series

10250T

Light unit type

Incandescent, full voltage

Type

30.5 mm, Heavy-Duty

Operating mode

Pull: maintained

Push: maintained

Illumination

Illuminated

Actuator

Side-lighted

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T579C63-13X



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)