

# Eaton 10250T580C48

Catalog Number: 10250T580C48

Eaton 30.5 mm Heavy-Duty Push-Pull Unit, Class I Division 2, Standard Actuator (Lens), Green, Plastic Bus, Illuminated, 120 MB Lamp, Incandescent, resistor, 120 Vac/Vdc Light Unit, Two-position, Maintained push and pull, 40 mm button, 10250T Series

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T580C48
UPC	Product Length/Depth
782113027531	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	
CSA Certified	
UL Listed	



## Product specifications

### Series

10250T

### Light unit type

Incandescent, resistor

### Number of positions

2

### Type

Class I Division 2

### Actuator color

Green

### Operating mode

Pull: maintained

Push: maintained

### Bus material

Plastic

### Light unit voltage

120 Vac/dc

### Rating

NEMA 13

NEMA 12

NEMA 4X

NEMA 4

NEC Class I Division 2, Groups B, C and D

NEMA 3

NEMA 3R

### Illumination

Illuminated

### Size

40 mm

### Actuator

Standard

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T580C48



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)