

Eaton 10250T580C63-1

Catalog Number: 10250T580C63-1

Eaton 10250T, 30.5 mm, Heavy-Duty, 40 mm, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, 2-position, Main. push and pull, Side-lighted, Red actuator, Anodized aluminum bus, EMERGENCY STOP, Incandescent, resistor light unit, 1NO-1NC, 120 Vac/dc LUV

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T580C63-1
UPC	Product Length/Depth
782113958538	2.63 in
Product Height	Product Width
1.78 in	1.78 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	UL Listed CSA Certified



Product specifications

Contact configuration

1 NO-1 NC

Number of positions

2

Actuator color

Red

Legend

EMERGENCY STOP

Bus material

Anodized aluminum

Light unit voltage

120 Vac/dc

Rating

NEMA 12

NEMA 3

NEMA 4

NEMA 3R

NEMA 13

NEMA 4X

Size

40 mm

Series

10250T

Light unit type

Incandescent, resistor

Type

30.5 mm, Heavy-Duty

Operating mode

Pull: maintained

Push: maintained

Illumination

Illuminated

Actuator

Side-lighted

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T580C63-1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)