

Eaton 10250T589

Catalog Number: 10250T589

Eaton 30.5 mm Heavy-Duty Watertight/Oiltight Push-Pull Unit, Class I Division 2, Illuminated, Lamp #755, Incandescent, transformer, 24 Vac Light Unit, Two-position, Maintained push and pull, 10250T Series

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T589
UPC	Product Length/Depth
782113776231	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	
UL Listed	
CSA Certified	



Product specifications

Series

10250T

Light unit type

Incandescent, transformer

Number of positions

2

Type

Class I Division 2

Operating mode

Pull: maintained

Push: maintained

Light unit voltage

24 Vac

Rating

NEMA 13

NEMA 3

NEMA 3R

NEMA 4X

NEC Class I Division 2, Groups B, C and D

NEMA 12

NEMA 4

Illumination

Illuminated

Size

40 mm

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T589