

Eaton 10250T5971FW

Catalog Number: 10250T5971FW

Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, 120 Vac with 6 Volt Lamp, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Two-position, Lever, White actuator, Incandescent, Transformer light unit

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T5971FW
UPC	Product Length/Depth
782113443331	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	
CSA Certified	
UL Listed	



Product specifications

Throw type

60 °

Light unit type

Incandescent, transformer

Number of positions

2

Series

10250T

Type

30.5 mm, Heavy-Duty

Actuator color

White

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Illuminated

Cam code

Cam 1

Voltage rating

120 V

Actuator

Lever

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T5971FW](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)