

Eaton 10250T597LES2A-1X

Catalog Number: 10250T597LES2A-1X

Eaton 30.5 mm Heavy-Duty Push-Pull, Assembled, Side-lighted 40 mm Actuator, Red, 1NO-1NC, Bayonet base, Illuminated, 120 Vac Lamp, EMERGENCY STOP, LED, full voltage, 24 Vac/Vdc Light Unit, Two-position, Main. Push/pull, 10250T Series

General specifications

| | |
|----------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton 10250T pushbutton | 10250T597LES2A-1X |
| UPC | Product Length/Depth |
| 782114713631 | 1 in |
| Product Height | Product Width |
| 1 in | 1 in |
| Product Diameter | Product Weight |
| 1.38 in | 0.1 lb |
| Warranty | Compliances |
| 1 year | CE Marked |
| Certifications | Catalog Notes |
| UL Listed CSA Certified | Assembled at Factory |



Product specifications

Contact configuration

1 NO-1 NC

Special features

Factory Assembled

Number of positions

2

Actuator color

Red

Legend

EMERGENCY STOP

Bus material

Anodized aluminum

Light unit voltage

120 Vac

Lamp voltage - min

120 VAC

Rating

NEMA 3

NEMA 3R

NEMA 12

NEMA 13

NEC Class I Division 2, Groups B, C and D

NEMA 4X

NEMA 4

Size

40 mm

Series

10250T

Lamp voltage - max

120 VAC

Light unit type

LED, full voltage

Type

Class I Division 2

Operating mode

Pull: maintained

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T597LES2A-1X

Push: maintained

Illumination

Illuminated

Actuator

Side-lighted



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)