

Eaton 10250T597LLS2A-1X

Catalog Number: 10250T597LLS2A-1X

Eaton 30.5 mm Heavy-Duty Push-Pull, Assembled, Side-lighted 40 mm Actuator, Blue, Anodized Aluminum bus, 1NO-1NC, Bayonet base, Illuminated, 120 Vac Lamp, LED, full voltage, 24 Vac/Vdc Light Unit, Two-position, Maintained push and pull, 10250T Series

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T597LLS2A-1X
UPC	Product Length/Depth
782114713655	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	Catalog Notes
UL Listed CSA Certified	Assembled at Factory



Product specifications

Contact configuration

1 NO-1 NC

Special features

Factory Assembled

Number of positions

2

Actuator color

Blue

Bus material

Anodized aluminum

Light unit voltage

120 Vac

Lamp voltage - min

120 VAC

Rating

NEMA 12

NEMA 3

NEMA 4

NEC Class I Division 2, Groups B, C and D

NEMA 4X

NEMA 13

NEMA 3R

Size

40 mm

Series

10250T

Lamp voltage - max

120 VAC

Light unit type

LED, full voltage

Type

Class I Division 2

Operating mode

Pull: maintained

Push: maintained

Illumination

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T597LLS2A-1X

Illuminated

Actuator

Side-lighted



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)