

# Eaton 10250T597LRH24-1X

Catalog Number: 10250T597LRH24-1X

Eaton 30.5 mm Heavy-Duty Push-Pull, Assembled, Heavy-Duty 40 mm Actuator, Red, Aluminum bus, 1NO-1NC, Bayonet base, Illuminated, 24 Vac/Vdc Lamp, LED, full voltage, 24 Vac/Vdc Light Unit, Two-position, Maintained push and pull, 10250T Series

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T597LRH24-1X
UPC	Product Length/Depth
782114713525	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	Catalog Notes
UL Listed CSA Certified	Assembled at Factory



## Product specifications

### Contact configuration

1 NO-1 NC

### Special features

Factory Assembled

### Number of positions

2

### Actuator color

Red

### Bus material

Heavy-duty aluminum

### Light unit voltage

24 Vac/dc

### Lamp voltage - min

24 V

### Rating

NEMA 4X

NEMA 12

NEC Class I Division 2, Groups B, C and D

NEMA 3R

NEMA 4

NEMA 13

NEMA 3

### Size

40 mm

### Series

10250T

### Lamp voltage - max

24 V

### Light unit type

LED, full voltage

### Type

Class I Division 2

### Operating mode

Push: maintained

Pull: maintained

### Illumination

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T597LRH24-1X

Illuminated

Actuator

Transparent center



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)