

# Eaton 10250T6033EG

Catalog Number: 10250T6033EG

Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, 120 Vac with 6 Volt Lamp, Cam 3, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Three-position, Knob, Green actuator, Incandescent, Transformer light unit

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T6033EG
UPC	Product Length/Depth
782113775944	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	
UL Listed	
CSA Certified	

## Product specifications

### Throw type

60 °

### Light unit type

Incandescent, transformer

### Number of positions

3

### Series

10250T

### Type

30.5 mm, Heavy-Duty

### Actuator color

Green

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Illuminated

### Cam code

Cam 3

### Voltage rating

120 V

### Actuator

Knob

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T6033EG



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia