

Eaton 10250T6087

Catalog Number: 10250T6087

Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, 24 Vac with 6 Volt Lamp, Cam 7, 40° throw, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Four-position, Incandescent, Transformer light unit

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T6087
UPC	Product Length/Depth
782113295206	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	
CSA Certified	
UL Listed	



Product specifications

Throw type

40 °

Light unit type

Incandescent, transformer

Number of positions

4

Series

10250T

Type

30.5 mm, Heavy-Duty

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Illuminated

Cam code

Cam 7

Voltage rating

24 V

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T6087



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia