

Eaton 10250T6232

Catalog Number: 10250T6232

Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, 120 Vac with 6 Volt Lamp, Cam 2, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Three-position, Incandescent, Transformer light unit

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T6232
UPC	Product Length/Depth
782113107585	3.6 in
Product Height	Product Width
2.1 in	2.3 in
Product Weight	Warranty
0.4 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified



Product specifications

Throw type

60 °

Light unit type

Incandescent, transformer

Number of positions

3

Series

10250T

Type

30.5 mm, Heavy-Duty

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Illuminated

Cam code

Cam 2

Voltage rating

120 V

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T6232



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia