

# Eaton 10250T6263

Catalog Number: 10250T6263

Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, Cam 3, 60° throw, 120 Vac with 6 Volt Lamp, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Three-position, Incandescent, Transformer light unit

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T6263
UPC	Product Length/Depth
782113295572	3.5 in
Product Height	Product Width
2.1 in	2.3 in
Product Weight	Warranty
0.4 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified



## Product specifications

### Throw type

60 °

### Light unit type

Incandescent, transformer

### Number of positions

3

### Series

10250T

### Type

30.5 mm, Heavy-Duty

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Illuminated

### Cam code

Cam 3

### Voltage rating

120 V

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T6263



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia