

# Eaton 10250T6383H

Catalog Number: 10250T6383H

Eaton 10250T pushbutton, 10250T, 30.5 mm, Class I Division 2, 120 Vac/dc, Cam 3, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Three-position, Incandescent, Full voltage light unit

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T6383H
UPC	Product Length/Depth
782114523735	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Certifications
1 year	UL 508 UL 1604

## Catalog Notes

Operator includes lens gasket and lens attachment screws



## Product specifications

### Throw type

60 °

### Light unit type

Incandescent, full voltage

### Number of positions

3

### Series

10250T

### Type

30.5 mm, Class I Division 2

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Illuminated

### Cam code

Cam 3

### Voltage rating

120 Vac/dc

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T6383H



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia