

# Eaton 10250T7019

Catalog Number: 10250T7019

Eaton 10250T pushbutton, Class I Division 2, NEMA 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D, Two-position, Maintained, Push-pull, jumbo mushroom head, Red actuator, Die cast enc., EMER. STOP (engraved button), 1NO-1NC

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T7019
UPC	Product Length/Depth
782114518359	0.25 in
Product Height	Product Width
4 in	3.88 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	
CE Marked	

## Product specifications

### Enclosure material

Die cast

### Contact configuration

1 NO-1 NC

### Series

10250T

### Number of positions

2

### Type

30.5 mm, Class I Division 2

### Actuator color

Red

### Operating mode

Maintained

### Legend

EMERGENCY STOP

### Number of elements

1

### Rating

NEMA 13

NEMA 4

NEC Class I Division 2, Groups B, C and D

NEMA 4X

NEMA 12

### Actuator

Push-pull, jumbo mushroom head

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T7019



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)