

# Eaton 10250T729BK

Catalog Number: 10250T729BK

10250T, Class I Div. 2, 30.5 mm, Selector switch, Knob, Spring return from left, Black, 1NO, 1NC-1NC, 1NO, Non-illuminated, Three-position, Cam 3, NEMA 3, 3R, 4, 4X, 12, 13

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton 10250T pushbutton	10250T729BK
<b>UPC</b>	<b>Product Length/Depth</b>
782114509753	1 in
<b>Product Height</b>	<b>Product Width</b>
1 in	1 in
<b>Product Weight</b>	<b>Warranty</b>
0.1 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	UL Listed
CE Marked	CSA Certified



## Product specifications

### Contact configuration

1 NO, 1 NC-1 NC, 1 NO

### Product category

Selector switch

### Series

10250T

### Number of positions

3

### Type

Knob

### Actuator color

Black

### Operating mode

Spring return from left

### Illumination

Non-illuminated

### Cam code

Cam 3

### Degree of protection

NEMA 13

NEMA 12

NEMA 4X

NEMA 3

NEMA 4

NEMA 3R

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T729BK