

# Eaton 10250T802AG

Catalog Number: 10250T802AG

Eaton 30.5 mm Heavy-Duty Pushbutton, Class I Division 2, Extended, Amber, Plastic Actuator, Chrome bezel, Zinc Die Cast bus, 1NO-1NC, Illuminated, Incandescent, transformer, 120 Vac Light Unit, Momentary, Guarded, 10250T Series

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T802AG
UPC	Product Length/Depth
782114514467	6.65 in
Product Height	Product Width
1.4 in	2 in
Product Weight	Warranty
0.7 lb	1 year
Compliances	Certifications
CE Marked	UL Listed CSA Certified



## Product specifications

### Contact configuration

1 NO-1 NC

### Actuator color

Amber

### Legend

Blank

### Actuator material

Plastic

### Light unit voltage

120 Vac

### Rating

NEMA 3

NEMA 12

NEC Class I Division 2, Groups B, C and D

NEMA 4

NEMA 4X

NEMA 13

NEMA 3R

### Bezel

Chrome

### Series

10250T

### Light unit type

Incandescent, transformer

### Type

30.5 mm, Class I Division 2

### Operating mode

Momentary

### Illumination

Illuminated

### Actuator

Extended, guarded

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T802AG



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)