

# Eaton 10250T818GD

Catalog Number: 10250T818GD

Eaton 10250T pushbutton, 30.5 mm, Class I Division 2, NEMA 3/3R/4/4X/12/13, NEC C1, D2, Groups B/C/D, Illum., Mom., Extended, Green actuator, Blank legend, Incand., FV light unit, 1NO-1NC, 24 Vac/dc LUV, Chrome bezel, Plastic actuator

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T818GD
UPC	Product Length/Depth
782114513576	2.87 in
Product Height	Product Width
1.38 in	1.38 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	
CE Marked	

## Product specifications

### Contact configuration

1 NO-1 NC

### Special features

10250T series

### Actuator color

Green

### Legend

Blank

### Actuator material

Plastic

### Light unit voltage

24 Vac/dc

### Lamp voltage - min

24 V

### Rating

NEC Class I Division 2, Groups B, C and D

NEMA 3R

NEMA 12

NEMA 4

NEMA 3

NEMA 4X

NEMA 13

### Bezel

Chrome

### Series

10250T

### Lamp voltage - max

24 V

### Light unit type

Incandescent, full voltage

### Type

30.5 mm, Class I Division 2

### Operating mode

Momentary

### Illumination

Illuminated

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T818GD

Application

Pushbutton

Actuator

Extended



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)