

Eaton 10250T828GD2A

Catalog Number: 10250T828GD2A

Eaton 10250T pushbutton, 30.5 mm, Class I Division 2, NEMA 3, 3R, 4, 4X, 12, 13, Illum., Mom., Extended, Green actuator, Blank legend, LED, FV light unit, 1NO-1NC, 6 Vac/dc LUV, Chrome bezel, 120 V lamp, Plastic actuator

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T828GD2A
UPC	Product Length/Depth
782114538180	2.87 in
Product Height	Product Width
1.38 in	1.38 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	
CE Marked	

Product specifications

Contact configuration

1 NO-1 NC

Special features

10250T series

Actuator color

Green

Legend

Blank

Actuator material

Plastic

Light unit voltage

6 Vac/dc

Lamp voltage - min

120 VAC

Rating

NEMA 12

NEMA 4X

NEMA 13

NEMA 4

NEMA 3

NEC Class I Division 2, Groups B, C and D

NEMA 3R

Bezel

Chrome

Series

10250T

Lamp voltage - max

120 VAC

Light unit type

LED, full voltage

Type

30.5 mm, Class I Division 2

Operating mode

Momentary

Illumination

Illuminated

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T828GD2A

Application

Pushbutton

Actuator

Extended



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)