

Eaton 10250T828GG24

Catalog Number: 10250T828GG24

Eaton 30.5 mm Heavy-Duty Pushbutton, Class I Division 2, Extended, Green, Plastic Actuator, Chrome bezel, Zinc Die Cast bus, 1NO-1NC, Bayonet base, Illuminated, LED, full voltage, 24 Vac/Vdc Light Unit, Momentary, Guarded, 10250T Series

General specifications

| | |
|-------------------------|----------------------------|
| Product Name | Catalog Number |
| Eaton 10250T pushbutton | 10250T828GG24 |
| UPC | Product Length/Depth |
| 782114539507 | 6.65 in |
| Product Height | Product Width |
| 1.4 in | 2 in |
| Product Weight | Warranty |
| 0.7 lb | 1 year |
| Compliances | Certifications |
| CE Marked | UL Listed CSA Certified |

Product specifications

Contact configuration

1 NO-1 NC

Actuator color

Green

Legend

Blank

Actuator material

Plastic

Light unit voltage

6 Vac/dc

Lamp voltage - min

24 V

Rating

NEMA 12

NEMA 3R

NEMA 4X

NEMA 13

NEMA 4

NEC Class I Division 2, Groups B, C and D

NEMA 3

Bezel

Chrome

Series

10250T

Lamp voltage - max

24 V

Light unit type

LED, full voltage

Type

30.5 mm, Class I Division 2

Operating mode

Momentary

Illumination

Illuminated

Actuator

Extended, guarded

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T828GG24



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)