

# Eaton 10250T849ES

Catalog Number: 10250T849ES

Eaton 10250T pushbutton, 10250T, 30.5 mm, , 40 mm, NEMA 3/3R/4/4X/12/13, NEC C1, D2, Groups B/C/D, Illum., Two-position, Main. push/pull, Side-lighted, Red actuator, Anodized aluminum bus, Incand., trans. light unit, 1NO-1NC, 24 Vac/dc LUV

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T849ES
UPC	Product Length/Depth
782114518755	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
3.79 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
	FDA 3-A
Certifications	
UL 1604	
UL 508	
CSA Certified	



## Product specifications

### Contact configuration

1 NO-1 NC

### Number of positions

2

### Actuator color

Red

### Legend

EMERGENCY STOP

### Bus material

Anodized aluminum

### Light unit voltage

24 Vac/dc

### Rating

NEMA 4

NEC Class I Division 2, Groups B, C and D

NEMA 4X

NEMA 3

NEMA 3R

NEMA 13

NEMA 12

### Size

40 mm

### Series

10250T

### Light unit type

Incandescent, transformer

### Type

30.5 mm, Class I Division 2

### Operating mode

Pull: maintained

Push: maintained

### Illumination

Illuminated

### Actuator

Side-lighted

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T849ES



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)