

Eaton 10250T853ED2A

Catalog Number: 10250T853ED2A

Eaton 10250T pushbutton, 10250T, 30.5 mm, Class I Division 2, 40 mm, NEMA 3/3R/4/4X/12/13, NEC C1, D2, Groups B/C/D, Illum., Main. push/pull, Std, Red actuator, Plastic bus, LED, FV light unit, 1NO-1NC, 120 Vac LUV, 120 Vac lamp

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T853ED2A
UPC	Product Length/Depth
782114541586	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
3.79 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
	FDA 3-A
Certifications	
CSA Certified	
UL 1604	
UL 508	



Product specifications

Resources

Contact configuration

1 NO-1 NC

Number of positions

2

Actuator color

Red

Legend

EMERGENCY STOP

Bus material

Plastic

Light unit voltage

120 Vac

Lamp voltage - min

120 VAC

Rating

NEMA 4

NEMA 3R

NEMA 3

NEC Class I Division 2, Groups B, C and D

NEMA 12

NEMA 4X

NEMA 13

Size

40 mm

Series

10250T

Lamp voltage - max

120 VAC

Light unit type

LED, full voltage

Type

30.5 mm, Class I Division 2

Operating mode

Pull: maintained

Push: maintained

Illumination

Illuminated

Actuator

Standard



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)