

Eaton 10250T875GD24

Catalog Number: 10250T875GD24

Eaton 30.5 mm Heavy-Duty Push-Pull Unit, Standard 40 mm Actuator, Green, Plastic Bus, 2NO-2NC, Illuminated, 24 Vac/Vdc Lamp, LED, full voltage, 24 Vac/Vdc Light Unit, Three-position, Maintained push and intermediate, momentary pull, 10250T Series

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T875GD24
UPC	Product Length/Depth
782114548837	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
	FDA 3-A
Certifications	
UL 508	
CSA Certified	
UL 1604	



Product specifications

Contact configuration

2 NO-2 NC

Number of positions

3

Actuator color

Green

Bus material

Plastic

Light unit voltage

24 Vac/dc

Lamp voltage - min

24 V

Rating

NEMA 4X

NEC Class I Division 2, Groups B, C and D

NEMA 3

NEMA 12

NEMA 13

NEMA 4

NEMA 3R

Size

40 mm

Series

10250T

Lamp voltage - max

24 V

Light unit type

LED, full voltage

Type

Class I Division 2

Operating mode

Push: maintained

Intermediate: maintained

Pull: momentary

Illumination

Illuminated

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T875GD24

Actuator
Standard



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)