

# Eaton 10250T886GH2A

Catalog Number: 10250T886GH2A

Eaton 30.5 mm Heavy-Duty Push-Pull Unit, Heavy-Duty 40 mm Actuator, Green, Aluminum bus, 1NO-1NC, Illuminated, 120 Vac Lamp, LED, full voltage, 120 Vac Light Unit, Three-position, Momentary push and pull, maintained intermediate, 10250T Series

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T886GH2A
UPC	Product Length/Depth
782114542316	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked FDA 3-A
Certifications	
UL 508 UL 1604 CSA Certified	



## Product specifications

### Contact configuration

1 NO-1 NC

### Number of positions

3

### Actuator color

Green

### Bus material

Heavy-duty aluminum

### Light unit voltage

120 Vac

### Lamp voltage - min

120 VAC

### Rating

NEMA 4X

NEMA 12

NEMA 13

NEMA 3R

NEC Class I Division 2, Groups B, C and D

NEMA 3

NEMA 4

### Size

40 mm

### Series

10250T

### Lamp voltage - max

120 VAC

### Light unit type

LED, full voltage

### Type

Class I Division 2

### Operating mode

Push: momentary

Intermediate: maintained

Pull: momentary

### Illumination

Illuminated

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T886GH2A

Actuator

Transparent center

---



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)