

Eaton 10250T886RH2A

Catalog Number: 10250T886RH2A

Eaton 30.5 mm Heavy-Duty Push-Pull Unit, Heavy-Duty 40 mm Actuator, Red, Aluminum bus, 1NO-1NC, Illuminated, 120 Vac Lamp, LED, full voltage, 120 Vac Light Unit, Three-position, Momentary push and pull, maintained intermediate, 10250T Series

General specifications

| | |
|-------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton 10250T pushbutton | 10250T886RH2A |
| UPC | Product Length/Depth |
| 782114542309 | 1 in |
| Product Height | Product Width |
| 1 in | 1 in |
| Product Diameter | Product Weight |
| 1.38 in | 0.1 lb |
| Warranty | Compliances |
| 1 year | FDA 3-A CE Marked |
| Certifications | |
| UL 508 | |
| UL 1604 | |
| CSA Certified | |



Product specifications

Contact configuration

1 NO-1 NC

Number of positions

3

Actuator color

Red

Bus material

Heavy-duty aluminum

Light unit voltage

120 Vac

Lamp voltage - min

120 VAC

Rating

NEMA 3R

NEMA 4X

NEC Class I Division 2, Groups B, C and D

NEMA 3

NEMA 13

NEMA 12

NEMA 4

Size

40 mm

Series

10250T

Lamp voltage - max

120 VAC

Light unit type

LED, full voltage

Type

Class I Division 2

Operating mode

Intermediate: maintained

Pull: momentary

Push: momentary

Illumination

Illuminated

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T886RH2A

Actuator

Transparent center



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)