

Eaton 10250T979C53-3X

Catalog Number: 10250T979C53-3X

10250T, 30.5 mm, Heavy-Duty, 40 mm, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Three-position, Maintained push, momentary pull, Standard, Red actuator, Plastic bus, EMERGENCY STOP, Incandescent, full voltage light unit, 2NC, 24 Vac/dc LUV

General specifications

| | |
|-------------------------|----------------------------|
| Product Name | Catalog Number |
| Eaton 10250T pushbutton | 10250T979C53-3X |
| UPC | Product Length/Depth |
| 782114707289 | 1 in |
| Product Height | Product Width |
| 1 in | 1 in |
| Product Weight | Warranty |
| 0.1 lb | 1 year |
| Compliances | Certifications |
| CE Marked | CSA Certified UL Listed |
| Catalog Notes | |
| Assembled at Factory | |



Product specifications

Contact configuration

2 NC

Number of positions

3

Actuator color

Red

Legend

EMERGENCY STOP

Bus material

Plastic

Light unit voltage

24 Vac/dc

Rating

NEMA 4X

NEMA 12

NEMA 13

NEMA 4

NEMA 3

NEMA 3R

Size

40 mm

Series

10250T

Light unit type

Incandescent, full voltage

Type

30.5 mm, Heavy-Duty

Operating mode

Pull: momentary

Push: maintained

Illumination

Illuminated

Actuator

Standard

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T979C53-3X



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)