

Eaton 10316H1028Y1

Catalog Number: 10316H1028Y1

10316 Series Cabinet Door Interlock, Cabinet Door Interlock, Zinc Plated Steel enclosure, 40A Make, 15A Break max AC, 0.5A Make, 0.5A Break max DC, 1NO-1NC, 40A Make, 15A Break at 120Vac, 0.5A Make and Break, Screw Terminals

General specifications



Product Name	Catalog Number
Eaton 10316 limit switch	10316H1028Y1
UPC	Product Length/Depth
782113492834	1.03 in
Product Height	Product Width
3.19 in	2.6 in
Product Weight	Warranty
0.3125 lb	1 year
Compliances	
Contact Manufacturer	

Product specifications

Enclosure material

Zinc plated steel

Contact configuration

1 NO-1 NC

Type

10316

Switch type

Cabinet door interlock

Contact Rating

40A MK, 15A BK at 120 Vac, 0.5A MK/BK at 120 Vdc

Maximum AC current

40 A make, 15 A break

Maximum DC current

0.5 A make, 0.5 A break

Connection

Screw terminal

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - 10316H1028Y1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)