

Eaton 13157RL07B1

Catalog Number: 13157RL07B1

Eaton OEM Prism 18mm tubular photoelectric sensor, OEM Prism Series Tubular Photoelectric Sensor, Right Angle, Sensor distance: 24 In., Iso SS Relay, 80 mA at 132 Vac/110 mA at 132Vdc, 4 Pin M12 Connector input

General specifications



Product Name	Catalog Number
Eaton OEM Prism 18mm tubular photoelectric sensor	13157RL07B1
	UPC
	782113493954
Product Length/Depth	Product Height
0.47 in	2.6 in
Product Width	Product Weight
0.71 in	1.313 lb
Warranty	Compliances
3 year	Contact Manufacturer

Product specifications

Contact configuration

Isolated solid state relay

Switch type

Photoelectric

Cord length

8 in

Maximum AC current

80 mA

Maximum DC current

110 mA

Operating temperature - min

-13 °F

Input voltage

10-30 Vdc

Connection

4-pin M12 connector

Cable type

Polyvinyl Chloride (PVC)

LED indicator

Output status: red

Enclosure material

Lens: polycarbonate

Body: structural polyurethane foam

Cable jacket: PVC

Operating mode

Diffuse reflective

Sensor type

Diffuse reflective

Contact Rating

80 mA at 132 Vac / 110 mA at 132Vdc

Operating temperature - max

131 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P,
NEMA 12, NEMA 13

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - 13157RL07B1](#)

Protection

Current limited for loads less than 32 Vac/dc



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)