

Eaton 1350E-8534

Catalog Number: 1350E-8534

Eaton Enhanced 50 Series Photoelectric Sensor, Photoelectric, Sensor dist. 5 Ft., 3A max AC, SPDT Form C Relay, 3A at 240 Vac, 5 Pin Dual Key Micro Pigtail Connector, 12–240 Vdc 24–240 Vac input

General specifications



| | |
|--|-----------------------------|
| Product Name | Catalog Number |
| Eaton Enhanced 50 photoelectric sensor | 1350E-8534 |
| UPC | Product Length/Depth |
| 782116111626 | 1.91 in |
| Product Height | Product Width |
| 3.46 in | 1.81 in |
| Product Weight | Warranty |
| 0.3375 lb | 3 year |
| Compliances | Certifications |
| Contact Manufacturer CE Marked | CSA Certified |

Product specifications

Contact configuration

SPDT form C relay

Switch type

Photoelectric

Cord length

6 ft

Maximum AC current

3 A

Operating temperature - min

-13 °F

Input voltage

12-240 Vdc, 24-240 Vac

Connection

5-pin dual key micro pigtail connector

Cable type

Polyvinyl Chloride (PVC)

LED indicator

Output status: green

Marginal gain: red

Power on: yellow

Enclosure material

Fiberglass reinforced plastic

Operating mode

Diffuse reflective

Sensor type

Diffuse reflective

Contact Rating

3A at 240 Vac

Operating temperature - max

131 °F

Environmental rating

IP67, IP69K

Time delay

Yes

Resources

Catalogs

Eaton's Volume 8—Sensing Solutions

Specifications and datasheets

Eaton Specification Sheet - 1350E-8534



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)