

Eaton 1624INT125B-1

Catalog Number: 1624INT125B-1

Eaton BR OEM interior assembly, BR style 1-inch loadcenter renewal part, interior assembly, 125A, single-phase, 24 circuits, 16 spaces, (1) 2/0-#14 AWG Cu/Al at 60°C or 75°C, aluminum bus, individual pack



General specifications

Product Name	Catalog Number
Eaton BR OEM interior assembly	1624INT125B-1
UPC	Product Length/Depth
782114884485	14.75 in
Product Height	Product Width
3.25 in	8.75 in
Product Weight	Warranty
3 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
Federal Specifications Classification W-P-115B, Type 1 and Class 2 Requirements	Contact Manufacturer
	Catalog Notes
	Individual pack

Product specifications

Number of spaces

16

Type

Interior assembly

Cover

Cover not included

Phase

Single-phase

Wire size

#14-2/0 AWG Cu/Al

Bus material

Aluminum

Number of wires

3

Number of circuits

24

Voltage rating

120/240 V

Amperage Rating

125A

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - 1624INT125B-1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)